

100%
Backwards
Backwards
Compatible



New features - but still the same



Improved materials KEMAR's previous fiber glass construction has been updated to a composite plastic construction that is more rugged and user friendly.



ear simulators Mount and dismantle the ear simulators with one hand for ear-canal exchange or calibration.

Snap fit



options KEMAR is delivered with two tripod adapters; one for a tripod with 3/8" thread and one for a Ø35 mm loudspeaker stand.



connections The internal cable connections have been moved to the neck for greater accessibility.

Convenient



The scalp is easily removed with the new release button which provides easy access to the inside of KFMAR.

1-Click access



vour needs KEMAR is available in several application specific configurations: assembled, calibrated and delivered as a complete out-of-thebox system for immediate use.