

GRAS 45BB-1

KEMAR Head & Torso for
Hearing Aid Test, 1-Ch LEMO



Connection: Traditional Power Supply (200 V/LEMO)

Channel(s): 1

ANSI: S3.36, S3.25

IEC: 60318-7, 60318-4

ITU-T Rec. P.57 Type 3.3

based on ITU-T Rec. P.58

The 45BB-1 Head & Torso for Hearing Aid test is configured with pinnae and with IEC 60318-4 Ear Simulator and ear canal extension in the right ear for testing of hearing aid. Due to the design of KEMAR, realistic measurement in a sound environment as experienced by a human being using a hearing aid is possible. Its CCP equivalent is [GRAS 45BB-2 KEMAR Head & Torso for Hearing Aid test, 1-Ch CCP](#).

Introduction

The KEMAR head and torso simulator was introduced by Knowles in 1972 and quickly became the industry standard for hearing-aid manufacturers and research audiologists (visit [KEMAR.us](https://www.kemar.us) to read the full story). It is based on worldwide average human male and female head and torso dimensions. It meets the requirements of ANSI S3.36/ASA58-2012 and IEC 60318-7:2011.

The current KEMAR Head and Torso has the same dimensions and acoustical properties as the original KEMAR, but has been developed further by GRAS to meet the industry's demand for realistic measurements of hearing aids, headphones and headsets. It provides acoustic diffraction similar to that encountered around the median human head and torso, both in the proximity and in the far field.

As all the preconfigured 45BB KEMARs consist of the same basic 45BB KEMAR Non-configured, plus a set of application specific accessories, the full information about a given KEMAR configuration is obtained by combining the information about the 45BB KEMAR Non-configured and the information for a given configured version as found in the present text. Read about the non-configured KEMAR [here](#).

Design

The 45BB-1 is a KEMAR head and torso for 1-channel hearing-aid test, with externally polarized ear simulator and large 55 Shore 00 pinnae.

It is delivered fully configured, individually calibrated and ready for use. In addition to a system calibration certificate, a USB flash memory with simulation data is included.

The main configuration specific components of the 45BB-1 are the GRAS RA0045 Ear Simulator

According to 60318-4 and the KB0066/KB50065 large pinnae.

The 60318-4 Ear Simulator

The acoustic input impedance of the RA0045 Ear Simulator closely resembles that of the human ear and, as a result, loads a sound source in very much the same way.

It complies with IEC 60318-4 and is measured and calibrated according to ITU-T P.57. It embodies a number of carefully designed volumes connected via well-defined and precisely tuned resistive grooves. In an equivalent electrical circuit, capacitors would represent the volumes, and inductance and resistance would represent respectively air mass and air flow within the resistive grooves.

Read more about RA0045 [here](#).

The KB0065/KB0066 Pinnae

The KB0065 and KB0066 are large straight pinnae for use with a straight ear canal extension. The hardness is 55 Shore 00. They comply with the IEC and ITU-T recommendations.

Even though 45BB-1 is configured for single-channel testing, both pinnae must be used to obtain correct diffraction around the head.

Other accessories for this configuration are listed in the Ordering Info tab.

Performance and warranty

KEMAR is made of components from our standard portfolio and are all manufactured of high-quality material and branded parts that were chosen and processed to ensure life-long stability and robustness. This, enables us to offer 2 years warranty against defective materials and

workmanship.

Exceptions: Microphones included in KEMAR as for these our normal 5 year warranty apply. The warranty period for cables is 6 months.

Connector type		7-pin LEMO (FGG.1B.307)
Set sensitivity @ 250 Hz (± 2 dB)	mV/Pa	12,5
Set sensitivity @ 250 Hz (± 2 dB)	dB re 1V/Pa	-38.5
Theoretical dynamic range lower limit with GRAS preamplifier	dB(A)	25
Theoretical dynamic range upper limit with GRAS preamplifier @ +28 V / ± 14 V power supply	dB	151
Theoretical dynamic range upper limit with GRAS preamplifier @ +120 V / ± 60 V power supply	dB	163
Resonance frequency	kHz	13.5
Temperature range, operation	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-30 to 60 / -22 to 140
Temperature range, storage	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-40 to 65 / -40 to 149
Humidity range non condensing	% RH	0 to 95%
ANSI standard		S3.36, S3.25
IEC standard		60318-7
CE/RoHS compliant/WEEE registered		Yes/Yes/Yes
Weight	g / oz	11.45 k / 404

GRAS Sound & Vibration reserves the right to change specifications and accessories without notice.

Included items

GRAS 45BB	KEMAR Head & Torso, non-configured
GRAS KB0065	KEMAR Large Right Pinna 55 Shore 00
GRAS KB0066	KEMAR Large Left Pinna 55 Shore 00
GRAS RA0237	Straight Ear Canal Extension Kit for KEMAR (2 pcs)
GRAS RA0045	IEC 60318-4 Ear Simulator
GRAS KB0110	Ear-mould Simulator for 2 mm I.D. Tubing
GRAS KB0111	Ear-mould Simulator for 3 mm I.D. Tubing
GRAS 26AS-S3	1/4" Preamp, Short version with 0.4 m cable
GRAS GR0010	Adapter for 1/2" Microphone and 1/4" Preamp
GRAS AA0008	LEMO 7-pin - LEMO 7-pin Cable, 3 m

Optional items

Power Modules for Externally Polarized Ear Simulators and Microphones

GRAS 12AK	1-Channel Power Module with gain, filters and SysCheck generator
GRAS 12AD	1-Channel Power Module
GRAS 12AA	2-Channel Power Module with gain, filters and SysCheck generator
GRAS 12AR	2-Channel Power Module
GRAS 12AQ	2-Channel Universal Power Module with signal conditioning and PC interface

For Ear Simulator Calibration

GRAS 42AP	Intelligent Pistonphone (250 Hz or 251.2 Hz, 114 dB +/- 0.05 dB)
GRAS 42AA	Pistonphone (250 Hz, 114 dB +/- 0.08 dB)
GRAS RA0157	1/2" Calibration Adapter for KEMAR Pinna

Pinna Simulators

GRAS KB0060	KEMAR Small Right Ear 55 Shore 00
-----------------------------	-----------------------------------

GRAS KB0061	KEMAR Small Left Ear 55 Shore 00
GRAS KB0065	KEMAR Large Right Ear 55 Shore 00
GRAS KB0066	KEMAR Large Left Ear 55 Shore 00
GRAS KB1060	KEMAR Small Right Ear, 35 Shore 00
GRAS KB1061	KEMAR Small Left Ear 35 Shore 00
GRAS KB1065	KEMAR Large Right Ear 35 Shore 00
GRAS KB1066	KEMAR Large Left Ear 35 Shore 00
GRAS KB0090	KEMAR Large Right Ear (VA-Style/SQ) 55 Shore 00
GRAS KB0091	KEMAR Large Left Ear (VA-Style/SQ) 55 Shore 00
GRAS KB1090	KEMAR Large Right Ear (VA-Style) 35 Shore 00
GRAS KB1091	KEMAR Large Left Ear (VA-Style) 35 Shore 00
GRAS KB5000	KEMAR Large Right Anthropometric Pinna 35 Shore 00
GRAS KB5001	KEMAR Large Left Anthropometric Pinna 35 Shore 00

Ear Mould Simulators

GRAS KB0110	Ear Mould Simulator for 2 mm Inner diameter tubing
GRAS KB0111	Ear Mould Simulator for 3 mm Inner diameter tubing

Ear Canal Extension and Microphone Holder Kits (kits with 2 pcs and O-rings)

GRAS RA0237	Straight Ear Canal Extension Kit for KEMAR
GRAS RA0238	VA-tapered Ear Canal Extension Kit for KEMAR
GRAS RA0239	Ear canal Extension Kit w. silicone lining for KEMAR
GRAS RA0240	Holder for long 1/2" microphone Kit for KEMAR
GRAS RA0241	Holder for short 1/2" microphone Kit for KEMAR
GRAS RA0243	Holder for 1/2" microphone Kit for KEMAR
GRAS RA0244	O-ring kit for KEMAR, 2 pcs.
GRAS RA0249	Straight Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test

GRAS RA0250	Tapered Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test
-------------	---

KEMAR Retrofit Kit for Binaural Hearing Aid Test

[GRAS RA0251](#)

KEMAR Retrofit Kit for Binaural Hearing Aid Test:
The Kit includes Ear Holder Plates, mounting bolts and the RA0249 and RA0250 Ear Canal Extension Kits. Included items are made of POM, Nylon and Teflon.

KEMAR Retrofit Kit for Anthropometric Pinna

[GRAS RA0311](#)

KEMAR Retrofit Kit for Anthropometric Pinna.
The Kit includes Ear Simulator Holder, 2 finger screws and a 3 mm Allen Key.

Extension Cables

[GRAS AA0008](#)

LEMO 7-pin - LEMO 7-pin Cable, 3 m

[GRAS AA0009](#)

LEMO 7-pin - LEMO 7-pin Cable, 10 m

[GRAS AA0020-
CL](#)

LEMO 7-pin - LEMO 7-pin Cable, Customized Length xxxx cm

Flight Case

GRAS KM0094

PELI Case for KEMAR

Simulation Model of KEMAR

GRAS KB3000

Simulation Model of KEMAR with large pinnae

GRAS KB3001

Simulation Model of KEMAR with small pinnae

Stand for KEMAR

GRAS AL0026

Loudspeaker stand for KEMAR, Ø 35 mm

Miscellaneous

GRAS KB0000

KEMAR Handbook

GRAS KB0010

T-Shirt for KEMAR

GRAS Sound & Vibration reserves the right to change accessories without notice.

We Make Microphones

Tradition

Since the establishment in 1994, GRAS has been 100% dedicated to developing and manufacturing high-quality measurement microphones and related acoustic equipment.

Innovation

We work with everybody with an interest in sound or noise within the fields of aerospace, automotive, audiology, consumer electronics, noise monitoring, building acoustics and telecommunications.

Quality

At GRAS we know that in order for you to trust your measurement results; signal quality, stability and robustness are essentials. We design and build them to perform under real life conditions – and beyond.

