

GRAS 45BC-10

KEMAR with Mouth Simulator
and Anthropometric Pinnae for
Headset Test, 2-Ch CCP



Connection: CCP
Channel(s): 2
Standards: ANSI: S3.36, S3.25
IEC: 60318-4, based on 60318-7
Based on ITU-T Rec. P.57 Type 3.3 and
ITU-T Rec. P.58
Special feature: Built-in power amplifier for
mouth simulator

The 45BC-10 KEMAR is configured with anthropometric pinnae and prepolarized IEC 60318-4 Ear Simulators. Due to its design, realistic measurement in a sound environment as experienced by a human being using a headset is possible. In addition, the 45BC-10 is provided with a mouth simulator for testing of the microphone in the headset. Its LEMO equivalent is [GRAS 45BC-9 KEMAR with Mouth Simulator and Anthropometric Pinna for Headset test, 2-Ch LEMO.](#)

Introduction

The KEMAR head and torso simulator was introduced by Knowles in 1972 and quickly became the industry standard for hearing-aid manufacturers and research audiologists (visit KEMAR.us to read the full story). It is based on worldwide average human male and female head and torso dimensions. It meets the requirements of ANSI S3.36/ASA58-2012 and IEC 60318-7:2011.

The current KEMAR Head and Torso has the same dimensions and acoustical properties as the original KEMAR, but has been developed further by GRAS to meet the industry's demand for realistic measurements of hearing aids, headphones and headsets. It provides acoustic diffraction similar to that encountered around the median human head and torso, both in the proximity and in the far field.

As all the preconfigured 45BB KEMARs consist of the same basic 45BB KEMAR Non-configured, plus a set of application specific accessories, the full information about a given KEMAR configuration is obtained by combining the information about the 45BB KEMAR Non-configured and the information for a given configured version as found in the present text. Read about the non-configured KEMAR [here](#).

Design

The 45BC-10 is a KEMAR with prepolarized ear simulators and anthropometric pinnae for 2-channel ear and headphone test.

It is delivered fully configured, individually calibrated and ready for use. In addition to a system calibration certificate, a USB flash memory with simulation data is included.

The main configuration specific components of the 45BC-10 are the GRAS RA0045-S1 Ear Simulator According to 60318-4 and the KB5000/KB50001

Anthropometric Pinnae.

The 44AA Mouth Simulator according to ITU-T Rec. P51 with built-in power amplifier

The maximum continuous signal the mouth can produce in 1/3-octave bands is 100dB re. 20 μ Pa in the frequency range 100Hz to 16kHz. Its loudspeaker accepts an external signal either directly or via its own built-in power amplifier (when power is applied).

The 60318-4 Ear Simulator

The acoustic input impedance of the RA0045-S1 Ear Simulator closely resembles that of the human ear and, as a result, loads a sound source in very much the same way.

It complies with IEC 60318-4 and is measured and calibrated according to ITU-T P.57. It embodies a number of carefully designed volumes connected via well-defined and precisely tuned resistive grooves. In an equivalent electrical circuit, capacitors would represent the volumes, and inductance and resistance would represent respectively air mass and air flow within the resistive grooves.

It is delivered with a built-in [GRAS 40A0](#) 1/2" prepolarized pressure microphone.

Read more about [RA0045-S1 Ear Simulator](#).

The Anthropometric Pinna

Compared to the standardized pinna, the anthropometric pinna embodies a number of improvements to the concha and ear canal, combined with increased collapsability of the helix, and improved mounting. It is made of soft silicone, 35 Shore 00 hardness.

The external shape of the pinna is identical to that of

the standardized KEMAR pinna, but concha and ear canal have been modified so that they closely mimic the properties of a real human ear. The ear canal has been extended and is now an integral part of the pinna, which seals directly against the ear simulator. Like the human ear, the ear canal has the 1st and 2nd bend, and the interface with the concha is oval. Fit and insertion consistency are much improved over the cylindrically or conically shaped ear canal extensions that are used with the standardized pinna.

The flexibility of the outer ear has been improved, and when mounting supra-aural and circum-aural headphones the pinna now collapses against the head very much like a human ear.

In addition to the traditional push mounting from the outside, the pinna is secured with two screws from the inside of KEMAR's head. These two screws ensure that the pinna is held firmly in place. Therefore, it seals perfectly against the ear simulator and the head, and it is therefore possible to mount and dismount DUTs repeatedly without compromising the seal.

Read more about the [Anthropometric Pinnae](#).

Typical Applications

The anatomical shape of the pinna makes it possible to achieve excellent fit and sealing with anatomically shaped in-ear transducers.

Controlling the insertion depth is easy, leading to good insertion consistency and highly improved repeatability and accuracy of measurements.

The improved fit and seal also means that the low frequency response is improved. It will allow you to reproduce bass notes, as well as effectively measure (active & passive) attenuation.

Therefore, the 45BC-10 KEMAR is ideal for accurate and repeatable testing of headphones, earphones and in-ear hearing protectors. In addition to this, the built-in mouth simulator makes it ideal for accurate and repeatable testing of headsets..

Performance and warranty

KEMAR is made of components from our standard portfolio and are all manufactured of high-quality material and branded parts that were chosen and processed to ensure life-long stability and robustness. This, enables us to offer 2 years warranty against defective materials and workmanship.

Exceptions: Microphones included in KEMAR as for these our normal 5 year warranty apply. The warranty period for cables is 6 months.

Connector type		BNC
Set sensitivity @ 250 Hz (± 2 dB)	mV/Pa	12.5
Set sensitivity @ 250 Hz (± 2 dB)	dB re 1V/Pa	-38.5
Theoretical dynamic range lower limit with GRAS preamplifier	dB(A)	25
Theoretical dynamic range upper limit with GRAS preamplifier @ +28 V / ± 14 V power supply	dB	151
Theoretical dynamic range upper limit with GRAS CCP preamplifier	dB	146
Resonance frequency	kHz	13.5
Temperature range, operation	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-30 to 60 / -22 to 140
Temperature range, storage	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-40 to 65 / -40 to 149
Humidity range non condensing	% RH	0 to 95%
ANSI standard		S3.36, S3.25
IEC standard		60318-7
ITU-T recommendations		P. 58
Weight	g / oz	11.45 k / 404
MOUTH SIMULATOR		.
Output impedance	Ω	8
Maximum power, continuous	W	10
Maximum power, pulsed 2 sec.	W	50
Input impedance	k Ω	20
Gain	dB	10
Input signal, max.	Vrms	2
Power supply, external	Vdc	24

GRAS Sound & Vibration reserves the right to change specifications without notice.

Included items

GRAS 45BC	KEMAR Head & Torso with GRAS 44AA Mouth Simulator , non-configured
GRAS KB5000	KEMAR Large Right Anthropometric Pinna 35 Shore 00
GRAS KB5001	KEMAR Large Left Anthropometric Pinna 35 Shore 00
GRAS GR0408	External Ear Canal (for calibration, 2 pcs)
GRAS GR0409	Union Nut (for GR0408, 2 pcs)
GRAS GR1874	Ear Simulator Holder (2 pcs)
GRAS RA0045-S1	IEC 60318-4 Ear Simulator, (Prepol.version, 2 pcs)
GRAS 26CS	1/4" CCP Standard Preamplifier with Microdot Connector, Very Short (2 pcs)
GRAS RA0001	Right Angled Adapter for 1/2" Microphone and 1/4" Preamplifier (2 pcs)
GRAS AA0018-S	Microdot-BNC Cable, 35 cm (2 pcs)
GRAS AA0035	3 m BNC - BNC Cable (2 pcs)
GRAS 46BD	1/4" CCP Pressure Standard Microphone Set
GRAS AA0070	Microdot-BNC Cable, 3 m

Optional items

Power Modules for Pre-polarized Ear Simulators and Microphones

GRAS 12AL	1-Channel CCP Power Module with A-weighting filter
GRAS 12AQ	2-Channel Universal Power Module with signal conditioning and PC interface

For Ear Simulator Calibration

GRAS 42AP	Intelligent Pistonphone (250 Hz or 251.2 Hz, 114 dB +/- 0.05 dB)
GRAS 42AA	Pistonphone (250 Hz, 114 dB +/- 0.08 dB)

Pinna Simulators

GRAS KB5000	Large Right Anthropometric Pinna 35 Shore 00
-----------------------------	--

GRAS KB5001	Large Right Anthropometric Pinna 35 Shore 00
GRAS KB0060	KEMAR Small Right Ear 55 Shore 00
GRAS KB0061	KEMAR Small Left Ear 55 Shore 00
GRAS KB0065	KEMAR Large Right Ear 55 Shore 00
GRAS KB0066	KEMAR Large Left Ear 55 Shore 00
GRAS KB1060	KEMAR Small Right Ear, 35 Shore 00
GRAS KB1061	KEMAR Small Left Ear 35 Shore 00
GRAS KB1065	KEMAR Large Right Ear 35 Shore 00
GRAS KB1066	KEMAR Large Left Ear 35 Shore 00
GRAS KB0090	KEMAR Large Right Ear (VA-Style/SQ) 55 Shore 00
GRAS KB0091	KEMAR Large Left Ear (VA-Style/SQ) 55 Shore 00
GRAS KB1090	KEMAR Large Right Ear (VA-Style) 35 Shore 00
GRAS KB1091	KEMAR Large Left Ear (VA-Style) 35 Shore 00

Ear Mould Simulators

GRAS KB0110	Ear Mould Simulator for 2 mm Inner diameter tubing
GRAS KB0111	Ear Mould Simulator for 3 mm Inner diameter tubing

Ear Canal Extension and Microphone Holder Kits (kits with 2 pcs and O-rings)

GRAS RA0237	Straight Ear Canal Extension Kit for KEMAR
GRAS RA0238	VA-tapered Ear Canal Extension Kit for KEMAR
GRAS RA0239	Ear canal Extension Kit w. silicone lining for KEMAR
GRAS RA0240	Holder for long 1/2" microphone Kit for KEMAR
GRAS RA0241	Holder for short 1/2" microphone Kit for KEMAR
GRAS RA0243	Holder for 1/2" microphone Kit for KEMAR
GRAS RA0244	O-ring kit for KEMAR, 2 pcs.
GRAS RA0249	Straight Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test

GRAS RA0250	Tapered Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test
-------------	---

KEMAR Retrofit Kit for Binaural Hearing Aid Test

[GRAS RA0251](#)

KEMAR Retrofit Kit for Binaural Hearing Aid Test:
The Kit includes Ear Holder Plates, mounting bolts and the RA0249 and RA0250 Ear Canal Extension Kits. Included items are made of POM, Nylon and Teflon.

Extension Cables

GRAS AA0034	BNC-BNC Cable, 2 m
-------------	--------------------

[GRAS AA0035](#)

BNC-BNC Cable, 3 m

GRAS AA0036	BNC-BNC Cable, 5 m
-------------	--------------------

[GRAS AA0037](#)

BNC-BNC Cable, 10 m

[GRAS AA0039-CL](#)

BNC-BNC Cable, Customized Length, xxxx cm

Flight Case

GRAS KM0094	PELI Case for KEMAR
-------------	---------------------

Stand for KEMAR

GRAS AL0026	Loudspeaker stand for KEMAR, Ø 35 mm
-------------	--------------------------------------

Miscellaneous

GRAS KB0000	KEMAR Handbook
-------------	----------------

GRAS KB0010	T-Shirt for KEMAR
-------------	-------------------

GRAS Sound & Vibration reserves the right to change accessories without notice.

| We Make Microphones

Tradition

Since the establishment in 1994, GRAS has been 100% dedicated to developing and manufacturing high-quality measurement microphones and related acoustic equipment.

Innovation

We work with everybody with an interest in sound or noise within the fields of aerospace, automotive, audiology, consumer electronics, noise monitoring, building acoustics and telecommunications.

Quality

At GRAS we know that in order for you to trust your measurement results; signal quality, stability and robustness are essentials. We design and build them to perform under real life conditions – and beyond.

